




POLAR KING MOBILE

Door Open Recovery Test

This test is conducted to simulate daily usage, as well as include frozen product within the unit, again in an effort to best simulate daily usage. In this test we pre-determined door openings to take place as shown on the attachment. Door disturbance means the tester walked in and out of the unit, at least once.

TEMP. (F)



TIME (Shown in minutes. Door was opened every 30 minutes.)

■ DOOR OPEN

■ DOOR OPEN - CURTAIN OPEN

■ DOOR OPEN - CURTAIN DISTURBED

— AMBIENT OUTSIDE TEMPERATURE

— 6' X 16' INSIDE TEMPERATURE

UNIT SPECS

Dimensions:

6' x 16'

Storage Space:

564 ft³

Temperature Range:

0° to 50°F

Refrigeration Unit:

GOVI Arktik 2000US

Electrical Requirements:

110v 15 amp Single Phase

UNIT CONSTRUCTION

4" thick (R-28) roof and walls

3/4" Keg Duty Floor

54" x 70" Door

2 5/16" Coupler



NSF, National Sanitation Foundation, is a non-profit organization founded in 1944, whose goal was to create standards for food safety and sanitation to promote public health. When you purchase NSF certified foodservice products, it means: The manufacturer of foodservice products uses only FDA approved raw materials.